



# DYNA-PRO®

www.saberindustrial.com

sales@saberindustrial.com

+961-9-546 540




## CRYSTAL SILICONE

One-part high modulus SUPER TRANSPARENT acetic curing silicone sealant for internal and external use. Excellent weather, aging and UV resistance.

Particularly good adhesion on glass and glazed surfaces.

**DYNA-PRO® Crystal Silicone** is ideal for use in areas requiring an aesthetically pleasing clear seal such as around glass and display cases.

### Approvals



## Features

- Crystal Clear Silicone
- Weather Resistant
- Aging Resistant
- UV Resistant
- Good Adhesion On Glass And Glazed Surfaces






## Surface Preparation

Surfaces must be clean, dry and free from all contaminants such as grease, rust, dust etc. To degrease, wipe with a pad soaked in solvent then wipe with a clean cloth. Remove dust with oil-free compressed air. In case of renovation work, old sealant as well as old paint must be removed completely.

## Instructions

Cut the nozzle at an angle and apply the sealant. Tool as required using a spatula dipped in soapy water. Application of the sealant during extreme temperature variations should be avoided.



## Technical Data

Property	Unit	Value
Application temperature	° C	+5 to +40
Application rate	g/min	1200
Density	g/ml	0.96
Skin over time	Min	10
Joint movement capability	%	25
Tensile Strength	Mpa	1.7
Elongation at break	%	700
Shore-A hardness (3 s)		14

## Priming

This product features adhesion to a variety of non-porous substrates; however, for specific substrates, priming may be necessary to improve adhesion. Please consult our Technical Service Department.

## Shelf Life

16 months from date of production, when stored at or below 30°C in the original unopened container

## Packaging

- 280 / 300 mL cartridge

## Standard Colors



Designed & Manufactured According to AFAQ  
ISO 9001:2015 Certified Quality Management System

*The information is offered in good faith and is believed to be accurate. It should not however be used in substitution for customer's tests to ensure that DYNA-PRO® products are safe, effective and compatible for the intended use. Sole warranty is that the product will meet the DYNA-PRO® sales specifications in effect at the time of delivery. Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.*